



### WOMEN WELFARE HYGIENIC PRODUCTS

**AN ISO & CE Certified** 

**MSME CERTIFIED** 

**GEM Registered Supplier** 



**Wisdom For Your Life** 



### Sanitary Napkin Incinerator

Wall Mountable & Front loading Pink Color fully Automatic machine









### Burning Capacity: 100 PADS/Day

80 to 100 Pads per day.

6-8 pads per cycle within 15 to 20 mins.

\*\*Insert up to 3 pads at a time.

Burning Capacity
80-100
PADS/DAY







#### **Dimensions**

Length 205mm x Breadth 205 mm x Height 435 mm Weight-11 Kg.





**Smoke** 

exhaust pipe

## Machine Features & Specification

- 01 Napkin Drop Point
- O2 Ash Collection Trey
- 03 Indicator
- 04 Start Push Button
- <sup>05</sup> Temp & Burning Time Display
- 06 Smoke exhaust pipe
- 07 MCB Control

Ash Collection
Trey

Ash Indicator

Start Push
Button

Temp & Burning
Time Display

MCB•



### Operating Mechanism Instruction for use:

Electric Socket board (16 Amp)

01): Connect the unit with supply through 16 AMP plug.

02): Turn "ON" MCB to start the machine.

03): Open the door & put the used napkin in drop point

04): Close the loading door properly

05): Press "PUSH" button for burn napkins

06): Wait for 15-20 minutes for burning napkin

07): Machine will shutdown automatically

(Auto turn off feature)

08): Ash collection tray for easy cleaning

Put Your Napkin here





# Easy Wall Mountable Using Screw


**Box Component & Accessories:** 











#### **More Information**



Mode Of Function	Electronically Operated, Fully Automatic
Color	Pink With Vinyl Branding Sticker
Electrical Part	800W Ceramic Heater, Power Supply 230v With Safety MCB (16Amp), Indicator, Push Button,
Machine Functioning	Burn Used Sanitary Napkins To Sterile Ash And Stop Automatically (Auto Turn Off Feature), Easy Removing Ash Collecting Tray Ensures Cleanliness.
Micro Controller	Provided Automatic Digital Display Controller To See Actual Set Timer And Temperature
Burning Waste	Completely Burn The Solid Napkin, Residue Ash Per Napkin Less Them 1 Milligram
Temperature	Minimum Burning Temperature 400 Degree Inner Burning Chamber And Skin Temperature Of The Unit Under Operation 16°C
Material Of Thermal Insulation	Double Thermal Insulation For Extra Protection Of Ceramic Fibre Board (Thickness: 25mm) & Glafibre Blanket (Density 64)
Machine Material	Mild Steel Boby With Epoxy Anti Rust Proof Powder Coated For Superior Finish ( DFT 100 Micron
Emission Outlet Pipe Location	Top Of Machine (To Be Supplied Along With Machine 5 Ft)
Warranty	12 Months Standard Brand Warranty
Type Of Packaging	Packing Of Thermocol And Carton Cardboard Fitment Box
Easy To Installtion	With The Help Of Mounting Accessories Provided , Hang The Machine On Wall & Start Collecting The Napkins.
Customer Support	24x7 Customer Support





# Thanks for connecting, us...

Office & Manufacturing Unit: VP INDUSTRIES.

AO-91, Amrit Steel Compound, South Side Industrial Area, Ghaziabad-201001

**AN ISO & CE Certified** 

**MSME CERTIFIED** 

**GEM Registered Supplier** 







